

2300N95 Disposable Respirator



STAY COOL ON THE JOB

Workers stay cooler with an exhale valve that reduces hot air build up. There's less breathing resistance and workers don't have to break midshift to cool off.

EASY FIT, MORE COMFORT

The molded nosebridge with soft foam nose cushion provides the wearer an easy, comfortable fit. There's no metal noseband to adjust and the seal is maintained without pressure points.

LAST LONGER, USE FEWER

The exclusive Dura-Mesh® shell protects the filter media so it stays cleaner-looking longer. The shell resists collapsing, even in heat and humidity so the respirator holds its shape longer. The result is fewer respirators used and lower costs.

SUITABLE FOR WELDING

2300 Series Particulate Respirators are suitable for most welding applications. The Dura-Mesh shell resists collapsing in hot humid conditions common to most welding applications. Meets heat and flame resistance in accordance with ANSI/ISEA 110.2003 Section 7.11.1.

APPLICATIONS

Hot, humid and dusty environments such as welding, soldering and brazing, grinding, sanding, sweeping, bagging, stone quarrying, metal machining, cement, underground mining, polishing, buffing, lime, poultry and textiles. No oils present.

FEATURES

- 100% PVC-Free.
- Available in three sizes to fit most workers in today's workplace.
- Exhale valve lets workers breathe easy and stay cool.
- Exclusive Dura-Mesh® shell resists collapsing in heat and humidity.
- Molded nosebridge seals easily and comfortably without a metal noseband.
- Facepiece is naturally contoured without pressure points.
- Soft, foam nose cushion for added comfort.
- Softspun® lining for increased comfort and durability.
- Suitable for most welding applications.
- Meets heat and flame resistance in accordance with ANSI/ISEA 110.2003 Section 7.11.1.



2350
Respirator
Locker



USE AGAINST:


1. Particulate aerosols free of oil.

DO NOT USE AGAINST:


1. Concentrations of contaminants which are unknown, or are immediately dangerous to life or health.
2. Concentrations of particulates which exceed the maximum use concentration or 10 times the OSHA Permissible Exposure Limit, whichever is lower.
3. Gases, vapors, asbestos, paint spray, sandblasting or particulate materials which generate harmful vapors.
4. Oil-based mists.

RESTRICTIONS

1. This respirator does not supply oxygen and must not be used in atmospheres containing less than 19.5% oxygen.
2. Do not remain in contaminated area if any physical distress occurs, for example breathing difficulty, dizziness or nausea.
3. Leave contaminated area and replace respirator if it is damaged, distorted, a proper fit can not be obtained or breathing becomes difficult.
4. Prior to each use, carefully inspect the entire respirator, including filter media and strap attachment area for tears and damage. Staple or strap attachment perforations do not effect NIOSH approval.
5. Do not alter, modify, or abuse this respirator.
6. Store unused respirators in box in a clean, dry, non-contaminated area.
7. Dispose of respirator according to your employer's policy and local regulations.
8. Dispose no later than thirty days after first use.
9. Use respirator before the "use by" expiration date printed on box.
10. If used for welding, wear appropriate eye and face protection.



Moldex-Metric, Inc.
CULVER CITY, CALIFORNIA, U.S.A.
800/421-0668



THESE RESPIRATORS ARE APPROVED ONLY IN THE FOLLOWING CONFIGURATIONS

TC-	PROTECTION ¹	RESPIRATOR		CAUTIONS AND LIMITATIONS ²
84A-0328	N95	2300N95	2301N95	2307N95
		X		X
			X	

1. Protection

N95 Particulate Filter (95% filter efficiency level) effective against particulate aerosols free of oil; time use restrictions may apply.

2. Cautions and Limitations

A- Not for use in atmospheres containing less than 19.5 percent oxygen.
 B- Not for use in atmospheres immediately dangerous to life or health.
 C- Do not exceed maximum use concentrations established by regulatory standards.
 J- Failure to properly use and maintain this product could result in injury or death.
 M- All approved respirators shall be selected, fitted, used, and maintained in accordance with MSHA, OSHA, and other applicable regulations.
 N- Never substitute, modify, add, or omit parts. Use only exact replacement parts in the configurations as specified by the manufacturer.
 O- Refer to user's instructions, and/or maintenance manuals for information on use and maintenance of these respirators.
 P- NIOSH does not evaluate respirators as surgical masks.

PACKAGING

2300N95-MED/LG, 2301N95-SM,
2307N95-LOW PROFILE
10 Respirators per Box
10 Boxes per Case

2350 Respirator Locker
5 Respirators per Locker
16 Lockers per Case

LIMITED WARRANTY IMPORTANT "NOTICE TO PURCHASER"

This limited warranty is made in lieu of the warranties of merchantability, fitness for particular purposes and all other warranties, express or implied. There are no other warranties which extend beyond the description on the face hereof. The physical standards and specifications of Moldex will be met by products sold. **Exclusive Remedies:** damages for the breach of this limited warranty are limited to the replacement of such quantity of Moldex products proved to be defectively manufactured. Except as provided above, Moldex shall not be liable or responsible for any loss, damages, or liability, direct, indirect, incidental, special or consequential, arising out of a sale, use or misuse, or the inability to use products by the user.

⚠ WARNING TO USER

1. Follow all instructions and warnings on the use of this respirator and wear during all times of exposure. Failure to do so will reduce respirator effectiveness, wearer protection, and may result in sickness or death.
2. Before use, the user must first be trained by the employer in proper respirator use, in accordance with applicable safety and health standards, for the contaminant and exposure level in the assigned work area.
3. The particulates and other contaminants which can be dangerous to your health include those which you cannot see, taste, or smell.
4. This product has not been sold with warnings or use instructions for personnel involved in health care or related situations, where there may be the possibility of contact with disease or biological hazards. If you are considering such uses, first call the Moldex Technical Service Dept., +1 (310) 837-6500 ext. 512/550 or +1 (800) 421-0668 ext. 512/550.

DISTRIBUTED BY:



Printed on Recycled Paper



MOLDEX
Ideas that wear well.